






PRODUCT NUMBER	PITCH
VExx32x100J0G	3.81 mm



SECTION Q-Q

RECOMMENDED P.C.B LAYOUT
TOP VIEW

SECTION P-P

Material:

- Item ③ Contact pin: Copper, Tin plated
 - Item ④ Terminal(housing): Thermoplastic (UL94V-0)
 - Item ⑤ With flange nut: Brass ,M2.5
- Electrical: cULus
- Voltage rating: 300V
 - Current rating: 8A
 - Withstanding Voltage: 1.6 KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: cULus

N=Number of poles

Dim L	NX3.81+10.39		
Dim B	(N-1)X3.81		
Dim C	(N-1)X3.81+9.0		
Dim D	(N-1)X3.81+3.9		

Poles	Dim B	Dim L & C	Dim D
2-5P	±0.10	±0.15	+0.35 -0
6-10P	±0.15	±0.20	
11-15P	±0.20	±0.25	
16-24P	±0.25	±0.35	

PART NO.: VE xx 32 x 1 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
02	2 poles	3 Black (RAL9005)	
03	3 poles	3 Red (RAL3001/D)	
...	...	3 Orange(RAL2011/P)	
24	24 poles	4 Yellow(RAL1018/A)	
		5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK											
ltr ecn no dr date				tolerances unless otherwise specified								title TERMINAL BLOCK									
				angles		linear		X.±0.5				PLUGGABLE SOCKET, VERTICAL, WITH FLANGE									
								X.X±0.3													
				X'±1"				X.XX±0.1		scale		dwg no									