

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RQ115-A2

BZ-2RQ115-A2

PAGE 1 OF 1

M

DRAWING
NUMBER

8

ISSUE

REVISIONS

A	CO 14866
17	O M W OCT 60
B	CO 34304
21	B E N JAN 75
C	CO - 73287-J
22	J A L NOV 93
D	CO - 77589
29	K D R MAR 94
E	CO-82133
30	CSL JUL 96
F	CO93346
12	D L T AUG 98

FORMTEK

0-50378

RELEASE NO.

REPLACES

CHECK

CHECK

CHECK

8 AUG 96


T S M

CHECK

60

17 OCT

O M W



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 9-13 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING -L9- 10 A - 125, 250, OR 480 VAC 1/2 A - 125 VDC; 1/4 A - 250 VDC	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
DIFFERENTIAL TRAVEL ----- .0004 - .002	-L 288-	ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .010 THREE PLACE (.000) ± .005 ANGLES ±
OVERTRAVEL ----- .219 MIN		WEIGHT .094 LB

