

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-3RD-A2**BZ-3RD-A2**

PAGE 1 OF 1

MDRAWING
NUMBER**6**

ISSUE

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	C017410
B	CO-73287-B
C	CO-77589
D	C093346


DLT
9 SEP 98

CHECK

L.S.D 17 JUN 63

G C H 15 MAY 63

DRAWN

FORMTEK
FO-50376

NOTE

⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 14 - 20 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	L96 15A 125, 250 OR 480 VAC 1/2A 125 VDC, 1/4A 250 VDC 1/8HP 125 VAC, 1/4HP 250 VAC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
DIFFERENTIAL TRAVEL ----- .0008 - .0030	L288 L299 L306	WEIGHT .064 LB
OVERTRAVEL ----- .060 MIN	CE Ⓣ Ⓢ 16A 250V ~ T85 5E4	