



Catalog No. FOR180-50-4

Description: CABLE TIE 50LB 180 YELLOW FOR ROLL

UPC No 786210814407

Home > Wire & Cable Management > Ty-Rap > Velcro Ties

FOR Roll Hook and Loop Tie, Yellow Polyethylene/Nylon for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 4572.0mm (180 Inches), Width of 19.05mm (0.75 Inch), Thickness of 1.588mm (0.0625 Inch), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

Descriptors

Category	Velcro Ties
Special Features	Enables quick and convenient bundling of data and fiber optic cables.

Specifications

Material	Polyethylene/Nylon
Color	Yellow
Lock Mechanism	Velcro Fastener
Tensile Strength	50 pounds , 222 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.75 in , 19.05 mm
Length	180 in , 4572 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant