






REV.	DATE	ECR NO.	DESCRIPTION
NC	03/25/04	XXXXXX	INITIAL RELEASE
A	03/27/05	XXXXXX	UPDATE PART DIMENSIONS/DRAWING FORMAT
B	12/17/10	2129	CHANGE TITLE BLOCK TO "MINI 75 OHM SMB R/A CRIMP PLUG"



RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex										
8	HEAT SHRINK TUBING			1		DRAWN	M.ZHANG	12/17/10												
7	COVER	BRASS	GOLD	1		CHECKED														
6	FERRULE	COPPER	GOLD	1		ISSUED				PART DESCRIPTION										
5	CONTACT PIN	BER. COPPER	GOLD	1		SHEET	1 OF 1				MINI 75 OHM SMB R/A CRIMP PLUG (FOR RG-179/U CABLE)									
4	INSULATOR	PTFE	NATURAL	1						PART NO.										
3	RETAINER RING	BER. COPPER	NATURAL	1						142194-75										
2	BODY	BRASS	GOLD	1						DWG. NO.										
1	HOUSING	ZINC DIECAST	GOLD	1		CAD FILE				142194-75.DWG										
DESCRIPTION MATERIAL FINISH QTY						C:/CONNEX/142194-75.DWG				REV.		B		SIZE		A		SCALE		NA