

USB-A to Lightning Sync/Charge Coiled Cable, MFi Certified - Black, M/M, USB 2.0, 4 ft. (1.22 m)

MODEL NUMBER: M100-004COIL-BK



Charge and sync your latest-generation iPhone, iPad and iPod using the USB-A port on your charger, laptop or desktop computer.

Description

The M100-004COIL-BK USB Sync/Charge Coiled Cable connects your latest-generation iPhone, iPad or iPod to the USB-A port on your USB charger, laptop or desktop computer, so you can charge your Apple device and transfer data at the same time. The cable features a reversible Lightning plug that connects to your Apple device in either direction, ensuring a fast, fumble-free connection.

The M100-004COIL-BK is MFi-certified for use with the latest generation of iPhone, iPad and iPod devices.

This four-foot cord is specially coiled to take up much less space than a normal cable, and has an effective length of 2-ft. (0.61 m) to 3-ft. (0.91 m) when in use. It also resists tangles and knots, making it convenient to store in your car or carry in your purse, backpack or laptop bag. Nickel-plated connectors ensure excellent conductivity, improving performance.

Features

Charge and Sync Your Latest-Generation iPhone, iPad and iPod USB-A male plug connects to charger, laptop or desktop computer's USB port Reversible Lightning male plug connects to Apple devices in either direction for fast, fumble-free connection

MFi-Certified for Device Compatibility Compatible with iPhone, iPad, iPad mini, iPad mini 2, iPad mini 3, iPad mini 4, iPad Air, iPad Air 2, iPad Pro 12.9 inch, iPad Pro 10.5 inch, iPad Pro 9.7 inch and iPod Touch devices with Lightning port

Coiled to Take Up Less Space than Regular Cable Effective length of 2 to 3-ft. (0.61 - 0.91 m) when in use Resists tangles and knots Stores perfectly in car, purse, backpack or laptop bag Nickel-plated connectors for excellent conductivity

Specifications

OVERVIEW	
UPC Code	037332192110

Highlights

- MFi-certified for use with iPhone, iPad and iPod devices
- Reversible Lightning plug connects in either direction
- Works with any computer or charger with a USB-A port
- 4 ft. cable is coiled to take up less space
- Effective length of 2-3-ft. (0.61 - 0.91 m) when in use
- Nickel-plated connectors

Applications

- Charge and sync your Apple iPhone, iPad or iPod using the USB-A port on your computer or a wall charger up to 4-ft. (1.22 m) away
- Transfer photos and other important files between an external hard drive and your Apple device

System Requirements

- Device or charger with USB-A port
- Most current iPhone, iPad and iPod devices

Package Includes

- M100-004COIL-BK USB Sync/Charge Coiled Cable with Lightning Connector (M/M), Black, 4-ft. (1.22 m)

Technology	Lightning; USB; USB 2.0 (High Speed)
USB Cable Type	Passive
INPUT	
Maximum Input Amps	2
POWER	
USB Power Delivery (PD) Charging Support	No
CHARGING	
Total Charging Watts	12
PHYSICAL	
Material of Construction	PU, PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.8mm
Wire Gauge (AWG)	28/22
Cable Length (ft.)	4
Cable Length (m)	1.22
Cable Length (in.)	48
Shipping Dimensions (hwd / in.)	4.57 x 2.40 x 0.91
Shipping Dimensions (hwd / cm)	11.61 x 6.10 x 2.31
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 176 F (-20 to 80 C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	12W (5V/2.4A)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)

Side B - Connector 1	LIGHTNING (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Data Transfer Rate	480 Mbps
USB Specification	USB 2.0 (up to 480 Mbps)
Angled Plug	No
STANDARDS & COMPLIANCE	
Product Certifications	MFi
Product Compliance	RoHS; REACH; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty