


1.Wiring Diagram.



2.Cable test condition :

Open / Short : 100%

Insulation resistance : 5M ohms

Contact resistance : 2 ohm

Hipot : DC 300V / 1 sec

3Each pcs with PE polybag.

4.For HDMI 2.0Ver.and Support Resolution ratio 3840x2160(4k)

And 60fps frame rate

NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF			2017/4/20
5	COPER	W20MM*L35MM	2		A		
4	PVC	45P PVC BLACK OVERMOLD	25g				
3	PE	LLDPE 500026 6201 INSIDE MOLDING	16g				
2	CONN	HDMI A TYPE MALE PIN G/F ,SHELL PLATED G/F, INSULATION BLACK	2	P1.P2	CnC Tech,LLC		TITLE HDMI A/M TO HDMI A/M CABLE
1	CABLE	UL20276 《28AWG (7/0.127TC) *1P+D+EA+AL/MY》 *5P+28AWG (7/0.127TC) *4C +AEM(16/8/0.12AM) OD7.3 BLACK HDMI2.0V.	1	1000mm	DRAWN EDWINLAI	DATE 2/28/17	DWN NO. 740-10012-00100
					CHECKED Win.C	2/28/17	CUSTOMER P/N:
					APPROVAL		CUSTOMER:
BILL OF MATERIAL					SHEET 1 OF 1		