Data Sheet | Item Number: 261-402

Jumper; for conductor entry; 2-way; insulated; gray

https://www.wago.com/261-402



Color: gray

Similar to illustration

Electrical data

Ratings per IEC/EN

Rated current	16 A

Physical data

Width	10 mm / 0.394 inches
Height	10 mm / 0.394 inches
Depth	4 mm / 0.157 inches
Jumper assignment	1-2

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.008 MJ
Weight	0.6 g

Environmental requirements

Processing temperature	-35 … +85 °C
Continuous operating temperature	-60 … +105 °C

Downloaded from Arrow.com.

Commercial data

Product Group	9 (Std Chassis Mt Blocks)
PU (SPU)	500 (25) pcs
Packaging type	Box
Country of origin	PL
GTIN	4045454033736
Customs tariff number	85366990990

Product classification

UNSPSC	39121410

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 261-402

Documentation

Additional Information

Technical Section	pdf 2246.92 KB	

Bid Text

261-402	19.02.2019	xml 2.62 KB
261-402	17.08.2017	doc 23.50 KB

CAD/CAE-Data

CAD data

2D/3D Models 261-402

CAE data

EPLAN Data Portal 261-402

WSCAD Universe 261-402

ZUKEN Portal 261-402

Downloaded from Arrow.com.

1 Compatible Products

1.1 Optional Accessories

1.1.1 Tool


1.1.1.1 Operating tool



Item No.: 209-132
Operating tool; for connecting comb-style jumper bar; made of insulating material; 2-way; natural

Installation Notes

Commoning



Commoning with comb-style jumper bar.

Downloaded from Arrow.com.