




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/23/10	
A		REDRAWN	11/23/10	
B		REVISED DIM.	3/31/11	
C		UPDATE SHAPE	9/23/14	AY/GC
D		UPDATE SPEC.	7/1/16	AY



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

A Voltage rating: 250 VAC/DC.

Current rating: 1A AC/DC.

Contact resistance: 1Ω max.

Insulation resistance: 100 MΩ min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions for .600 [15.24] spacing: 24, 28, 32, 36, 40

A = .100 [2.54] x No. of Spaces

B = .100 [2.54] x No. of Spaces + .307 [7.80]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	SS	8/23/10
CHECKED		
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
 FLAT CABLE DIP PLUG, .100 [2.54mm]
 .600 [15.24mm] ROW TO ROW

SIZE X	PART NO. FDP-6XX-T	REV. D
REF: S00040T	SCALE: NTS	SHEET 1 OF 1