

Product data sheet

Specifications

APC IT Power Distribution Module 3 Pole 5 Wire 20A L21-20 440cm



PDM3520L2120-440

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	120 V
Provided equipment	Installation guide

Physical

Colour	Black
Height	12.7 cm
Width	44.5 cm
Depth	40.6 cm
Net weight	4.45 kg

Input

Network frequency	60 Hz
Permissible voltage	200...240 V
Max line current	20 A

Output

Max current draw	20 A
Number of power socket outlets	1 NEMA L21-20

Conformance

Product certifications	UL listed
-------------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	40.6 cm

Package 1 Length 44.5 cm

Package 1 Weight 5 kg

Contractual warranty

Warranty 1 year repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **No**

EU RoHS Directive **Under investigation**

Use Again

Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back **Yes**

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins