



Part Number : [1300980037](#)

Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 1.57-3.18mm (.062-.125"), Stainless Steel

Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Part Number : 5518SS



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 1.57-3.18mm (.062-.125"), Stainless Steel
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678835896

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	1.57-3.18mm (.062-.125")
Color - Grommet	Black
Eye Type	N/A
Gender	Male
Material - Body	Stainless Steel
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	1300990143
MAX-LOC Gasket Sealing Ring,	1300990149

1/2" NPT, Black	
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Dec 30, 2025