

Catalog No. 54872BE

Description: LNG BAR 350 1/2 BH ON 1-3/4 TIN PLT

UPC No 786210898070

Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper Two-Hole Lug, Long Barrel, Blind End, Max 35kV, Wire Size 350 kcmil, 1/2 Inch Bolt Size, 1-3/4 Inch Hole Spacing, Tin Plated, Die Code 71, Die Color Code Red

Representative Image

Descriptors

Category	Cable or wire lug
----------	-------------------

Specifications

Cable Size	350 kcmil
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Red

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809 UL E9809

Dimensions

Stud Size	1/2 in
-----------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	N

by ABB

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	2
AWG size	350 kcmil