


Rev	AWO #	Description	Date	Appr
-		RELEASED	3/13/20	

APPROVED: _____


DATE: _____ TITLE: _____







RECOMMENDED P.C.B LAYOUT



SPECIFICATIONS:
Material:
Housing: Hi–Temp Thermoplastic, rated UL94V–0, Color: Black
Contact: Phosphor Bronze, Tin plated
Electrical:
Contact resistance: 30 Milliohms max
Insulation resistance: 1,000 Megaohms ohms min
Dielectric Voltage: 500 VAC @ sea level
Temperature Rating:
Operating temperature: –25°C to +85°C
Environmental:
Lead free, RoHS compliant RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

MM		ANGLE	
X	± 0.30	X	± 1°
X.X	± 0.25	X.X	± 0.5°
X.XX	± 0.20		
X.XXX	± 0.10		

APPROVALS		DATE
DRAWN	LH	3/13/20
CHECKED	MY	3/13/20
APPROVED		

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: COIN CELL BATTERY HOLDER FOR CELL CR2032, SMT TYPE, COLOR: BLACK

SIZE	PART NO.	REV.
X	BH-49A-5-T-BK	-

REF: S00136C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.