



Part Number : [451110301](#)
Product Description : Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf (OTS) Cable Assembly, 1.25mm Pitch, Single Row, 100.00mm Length, 3 Circuits, Black
Series Number : 45111
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

[451110301 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	45111
Description	Micro-Lock Plus-to-Micro-Lock Plus Off-the-Shelf (OTS) Cable Assembly, 1.25mm Pitch, Single Row, 100.00mm Length, 3 Circuits, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Lock Plus Both Ends
Keyword	Micro-Lock Plus 1.25
Product Name	Micro-Lock Plus
Type	Discrete Wire Assembly
UPC	191128368452

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Physical

Cable Length	100.00mm
Circuits (Loaded)	3
Circuits (maximum)	3

Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	0.950/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	26

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	<u>505568</u>
1.25mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	<u>505567</u>

This document was generated on Apr 15, 2026