


TE CONNECTIVITY (N) | Product | +1 800 522 6752 | Cart
English (EN) | United States (US)

TE
All Products | Search by part # or keyword
Log In/Register | My Account | Cart

Products
Industries
Services & Trainings
Tools & Resources
About TE
Sustainability
Shop TE Store

Connectors > Automotive Connectors > Data Connectivity Systems > Data Connectivity Housings
2324319-9



**2324319-9**  
2 Code, Housing for Female Terminals, 40 - 105 °C (40 - 221 °F), Data Connectivity Housings

TE Internal #: 2324319-9  
TE Internal Description: 3-PORT MATENET FRAMELTP9 COD

Settable: No  
Connector & Keying Code: Z  
Connector & Housing Type: Housing for Female Terminals  
Operating Temperature (Max): 105 °C (221 °F)  
Operating Temperature Range: 40 - 105 °C (40 - 221 °F)

[Add to List](#) | [Similar Products](#) | [Digital Download](#)

[Compatible Parts & Testing](#)

**300 Parts in Stock**

2 Code, Housing for Female Terminals, 40 - 105 °C (40 - 221 °F)...

TE Part #: 2324319-9  
[View Product](#)

180° Cable Exit, 4 Position, 8 Code, Housing for Female...

TE Part #: 2324102-2  
[View Product](#)

**We are here to help!**  
Get in touch with our product experts.

[CHAT WITH US](#)

[EMAIL US](#)

[CALL US](#)

Documents
Features
Product Compliance

**CAD Files**

Download ECAD Model File

[Reset Free CAD Models](#)  
Learn more about the ECAD Model 3D tool

Download the New Library Loader to convert 3D file to your ECAD Tool.

3D\_CAD\_CRM\_2324319-9\_A.pptf  
3D

Customer View Model

ENH\_CRM\_CRM\_2324319-9\_A\_M\_drl.zip  
English

ENH\_CRM\_CRM\_2324319-9\_A\_M\_dgn.zip  
English

ENH\_CRM\_CRM\_2324319-9\_A\_M\_dwg.zip  
English

**Product Specifications**

Application Specifications

ENH\_SL\_114-9423\_E.pdf  
English

Product Specification

ENH\_SL\_108-9468\_A1.pdf  
English

**Product Change Notification**

View Product Change Notification

Login required to access product change notifications

[REPORT PRODUCT DATA ERROR](#)

**Compatible Parts**

2324319-9

3-PORT MATENET FRAMELTP9 COD

[View Product](#)


[Filter By Specification](#)

Products with Similar Specs
[View All Similar Products](#)

**THIS PRODUCT**

2324319-9

2 Code, Housing for Female Terminals, 40 - 105 °C (40 - 221 °F)...




Settable: No  
Connector & Keying Code: Z  
Connector & Housing Type: Housing for Female Terminals  
Operating Temperature (Max): 105 °C  
Operating Temperature Range: 40 - 105 °C

**Non-Stocked**

**TOP RESULTS**

2324319-9

2 Code, Housing for Female Terminals, 40 - 105 °C (40 - 221 °F)...




Settable: No  
Connector & Keying Code: Z  
Connector & Housing Type: Housing for Female Terminals  
Operating Temperature (Max): 105 °C  
Operating Temperature Range: 40 - 105 °C

**In Stock**

2324102-2

180° Cable Exit, 4 Position, 8 Code, Housing for Female Terminals...




Settable: No  
Cable Exit Style: 180°  
Number of Positions: 4  
Connector & Keying Code: B  
Settable: No

**In Stock**

2324319-3

2 Code, Housing for Female Terminals, 40 - 105 °C (40 - 221 °F)...



Settable: No  
Connector & Keying Code: C  
Connector & Housing Type: Housing for Female Terminals  
Operating Temperature (Max): 105 °C  
Operating Temperature Range: 40 - 105 °C

**Non-Stocked**

**Contact Our Team - 24/7 Support**

+1 800 522 6752

[Chat](#)

[Submit Feedback](#)

See Support Details

[Connect With Us](#)

[Facebook](#) | [Twitter](#) | [LinkedIn](#) | [YouTube](#)

**Access Further Information**

Distributors

Suppliers

Supplier Directory

**Get Answers Now**

Authorized Distributors & Resellers

Product FAQs

Temple FAQs

TE Store FAQs

Terms and Conditions of Sale

Sample Terms and Conditions

**Select Your Preferences**

**Language**

English (EN)

**Ship to**

United States (US/US)

TE Connectivity empowers engineers by designing and manufacturing sensor and connectivity solutions for our increasingly connected world.

[Terms of Use](#) | [Privacy](#) | [GDPR Policy](#) | [Cookie Policy](#) | [Accessibility](#) | [Security](#) | [Site Map](#) | © 2023 TE Connectivity, All Rights Reserved.

Facebook

Facebook

Facebook