

561 Series > 5610043801F

General Description	
Viewing	
Sizes	
Series	561
RoHS	YES
RelatedProducts	
Polarity	
Part Number	5610043801F
PackageOptions	
LensStyle	
LampType	
Diffused	
Description	CUSTOM LED ASSEMBLY
Configuration	
Color	
ViewingAngle	



Absolute Maximum Ratings (Ta = 25℃)	
StorageTemp	
SolderTemp	
OperatingTemp	
ForwardCurrent_mA	
Derating	

Package Outlines

3D IGES File

3D STEP File

check stock

Operating Characteristics	
TestCurrent_mA	
PowerDissipationMax	
PeakWaveLength	
LuminousIntensityTyp	
LuminousIntensityMin	
LuminousIntensityMax	
LEDType	
FwdVoltageTyp	
FwdVoltageMin	
FwdVoltageMax	
EmittedColor	
Color	