



+ CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
GET - 50 way PCM assy, key C
[Get .64 Connector System](#)

1438693-1
TE Internal Number: 1438693-1

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Connector Style** Housing for female terminals
- Mating Tab Width (mm)** .64, 1.5
- Mating Tab Width (in)** .025, .059
- Connector System** Wire-to-Wire
- Number of Positions** 50
- Centerline (Pitch) (mm)** 2.54, 5.08
- Centerline (Pitch) (in)** .1, .2

 **PRODUCT DRAWING**
[English](#)

 **3D PDF**

DOCUMENTATION

Product Drawings

PCM 50-WAY HARNESS ASSEMBLY KEY C
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

3D_STP.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

2D_DXF.ZIP

English

Instruction Sheets

Instruction Sheet (U.S.)

PCM2003 Harness Assemblies

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Housing for female terminals

Connector System Wire-to-Wire

Sealable Yes

Hybrid Connector Yes

Primary Locking Feature Integrated in Housing

Strain Relief Add By Accessory

Row-to-Row Spacing 4.7 mm [.185 in]

Configuration Features

Number of Positions 50

Number of Rows 1, 4

Body Features

Color Black

Cable Exit Angle 180°

Body Material PA GF

Contact Features

Mating Tab Width (mm) .64, 1.5

Mating Tab Width (in) .025, .059

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Centerline (Pitch) (mm) 2.54, 5.08
Centerline (Pitch) (in) .1, .2

Dimensions

Width 52.9 mm [2.083 in]
Height 46.5 mm [1.831 in]
Length 40.8 mm [1.606 in]

Usage Conditions

Operating Temperature Range -40 – 125 °C [-40 – 257 °F]

Operation/Application

Circuit Application Signal

Industry Standards

Degree of Protection IP67

Packaging Features

Packaging Method Package
Packaging Quantity 40

Other

Connector Position Assurance Capable No
Serviceable Yes

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF