

Color:  white

Electrical data	
Rated current	140 A

Physical data	
Length	1000 mm

Material data	
Color	white
Fire load	0 MJ
Weight	266 g

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454229443
Customs tariff number	7407100000

Product classification	
UNSPSC	39121613
eCl@ss 10.0	27-14-11-39
eCl@ss 9.0	27-14-11-39
ETIM 9.0	EC000485
ETIM 8.0	EC000485
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 210-133	<a href="#">↓</a>

Documentation

Bid Text			
210-133	19.02.2019	xml 2.54 KB	<a href="#">↓</a>
210-133	23.11.2018	docx 13.39 KB	<a href="#">↓</a>

CAD/CAE-Data

CAD data	
2D/3D Models 210-133	<a href="#">↓</a>

CAE data	
EPLAN Data Portal 210-133	<a href="#">↓</a>
WSCAD Universe 210-133	<a href="#">↓</a>
ZUKEN Portal 210-133	<a href="#">↓</a>

1 Compatible Products

1.1 Optional Accessories

























1.1.1 Cover

1.1.1.1 Cover



<b>Item No.: 777-303</b>
N-busbar cover; 1000 mm long; transparent



1.1.2 N-busbar			
1.1.2.1 Busbar terminal block			
			
<a href="#">Item No.: 210-281</a> Connector; blue	<a href="#">Item No.: 209-105</a> Connector; silver-colored		
1.1.3 Shield termination			
1.1.3.1 Shield clamping saddles			
			
<a href="#">Item No.: 790-108</a> Shield clamping saddle; 11 mm wide; diameter of compatible conductor; 3 ... 8 mm	<a href="#">Item No.: 790-208</a> Shield clamping saddle; 12.4 mm wide; 3 ... 8 mm	<a href="#">Item No.: 790-116</a> Shield clamping saddle; 19 mm wide; diameter of compatible conductor; 7 ... 16 mm	<a href="#">Item No.: 790-216</a> Shield clamping saddle; 21.8 mm wide; 6 ... 16 mm
			
<a href="#">Item No.: 790-124</a> Shield clamping saddle; 27 mm wide; diameter of compatible conductor; 6 ... 24 mm	<a href="#">Item No.: 790-220</a> Shield clamping saddle; 30 mm wide; 6 ... 20 mm	<a href="#">Item No.: 790-140</a> Shield clamping saddle; diameter of compatible conductor	
1.1.3.2 Shield termination			
			
<a href="#">Item No.: 791-107</a> Shield clamp; diameter of compatible conductor; 1.5 mm to 6.5 mm; H max. 40 mm; 10 mm wide	<a href="#">Item No.: 791-117</a> Shield clamp; diameter of compatible conductor; 10 mm to 17 mm; H max. 63 mm; 23 mm wide	<a href="#">Item No.: 791-124</a> Shield clamp; diameter of compatible conductor; 16 mm to 24 mm; H max. 78 mm; 30 mm wide	<a href="#">Item No.: 791-111</a> Shield clamp; diameter of compatible conductor; 5 mm to 11 mm; H max. 47 mm; 17 mm wide
			
<a href="#">Item No.: 790-398</a> T-connector; for busbars Cu 10 mm x 3 mm; silver-colored			
1.1.4 Terminal blocks			
1.1.4.1 Common potential terminal block			
			
<a href="#">Item No.: 812-111</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; CAGE CLAMP®; 16,00 mm²; light gray	<a href="#">Item No.: 812-114</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; CAGE CLAMP®; blue	<a href="#">Item No.: 812-112</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; CAGE CLAMP®; dark gray	<a href="#">Item No.: 812-113</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; CAGE CLAMP®; red
			
<a href="#">Item No.: 812-104</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; Push-in CAGE CLAMP®; 4,00 mm²; blue	<a href="#">Item No.: 812-101</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; Push-in CAGE CLAMP®; 4,00 mm²; light gray	<a href="#">Item No.: 812-102</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; Push-in CAGE CLAMP®; dark gray	<a href="#">Item No.: 812-103</a> Busbar terminal block; for (10 x 3) mm busbars; without push-buttons; Push-in CAGE CLAMP®; red
			
<a href="#">Item No.: 812-110</a> Ground busbar terminal block; for (10 x 3) mm busbars; CAGE CLAMP®; green-yellow	<a href="#">Item No.: 812-100</a> Ground busbar terminal block; for (10 x 3) mm busbars; Push-in CAGE CLAMP®; 4,00 mm²; green-yellow		

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: [www.wago.com](http://www.wago.com)