

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

LOC	DIST
G	14

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECO–11–004820	11MAR11	RK	HMR





1. INSULATION DIA .170 MAX
2. FITS TAB .020 THK

–	–	–
100	LOOSE PC,BOX	8–640919–1
–	TAPE MOUNTED	640919–2
–	LOOSE PIECE	640919–1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1–800–522–6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1–800–722–1111
FOR ORDER ENTRY	1–800–526–5142

MAX RECOMMENDED OPERATING TEMPERATURE: –

VOLTAGE RATING: – –

CIRCULAR MIL AREA: – –

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± .015
3 PLC	± –
4 PLC	± –
ANGLES	± –

MATERIAL: BODY,BRASS .016
SLV,NYLON,COLOR,BLUE

FINISH: BODY,TIN

DWN	L OLMEDA	26JUN95
CHK	M ELLIS	26JUN95
APVD	B BARE	26JUN95
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME: RECEPTACLE, 187 SERIES, FASTON™, PIDG™, WIRE SIZE 16–14

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C–640919	—

CUSTOMER DRAWING | SCALE NTS | SHEET 1 OF 1 | REV G1

1470–19 (3/11)

Downloaded from Arrow.com.