

010 - 0081 - 0000 Product Details

No Image Available

010 - 0081 - 0000
(4 - 1532129 - 4)
Active

SMB RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

Housing Crimp Tool

Jack, Plug

Miniature

Terminate To Coaxial Cable

Coupler Style = Threaded

View all Features | Find Similar Products

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri

Quick Links

Check Pricing & Availability

Search for Tooling Product Feature Selector

Contact Us About This Product

Documentation & Additional Information	
Product Drawings: None Available Catalog Pages/Data Sheets: None Available Product Specifications: None Available Application Specifications: None Available Instruction Sheets: None Available CAD Files: None Available	Additional Information: Product Line Information Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Product Type = Housing Crimp Tool Gender = Jack, Plug Connector Series = Miniature Grade = Commercial Termination Related Features: Coaxial Cable Termination Type = Crimp Body Related Features: Coupler Style = Threaded Body Plating = Gold per MIL -G-45204, Type II, Grade C, Class 1 Cable Jacket Diameter (mm [in]) = 2.24 [0.088]	Contact Related Features: Center Contact Plating = Gold per MIL -G-45204, Type II, Grade C, Class 1 Contacts = With Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: Terminate To = Coaxial Cable Other: Brand = Microdot

Provide Website Feedback | Contact Customer Support

Home | Customer Support | Suppliers | Site Map | Privacy Policy | Browser Support

© 2008 Tyco Electronics Corporation All Rights Reserved

Downloaded from Arrow.com