

BU-31602-@

(Press-fit, UL® Listed Banana Jack with Solder Pin Connection)



- The BU-31602 is a press-fit, front install UL® listed 4mm banana jack. Accepts shrouded, unshrouded, and retractable 4mm banana plugs.
- Mounting: Can be mounted on panels up to 1.0" (25.4mm) thick with a recommended mounting hole of $\varnothing 7/16$ " (11.2mm).
- Overall length 1.25" (31.8mm), pin length = 0.23" (5.8mm), pin $\varnothing$ = 0.078"
- Connect wire via solder pin connection.
- Material: Housing Nylon
 Contacts Nickel-plated brass
- Ratings: Current 15 Amps
 Voltage 1000V, CAT III
- Colors: The "@" in the part number indicates color. Standard colors are:
 -0 Black, -2 Red
- RoHS 3 compliant (exemption 6c), CE Certified