

Part Number: 5034802600

**Product Description:** Easy-On FFC/FPC Connector, 0.50mm Pitch, FBH1 Series, Right-Angle, Dual Contact, 1.00mm Height, 26 Circuits, Gold over Nickel Plating

Series Number: 503480

**Status:** Active

**Product Category:** FFC / FPC Connectors



#### **Documents & Resources**

### **Drawings**

5034802600 sd.pdf

**3D Models and Design Files** 

STEP AP242

**SOLIDWORKS** 

Creo

Symbol and Footprint (Multi-Format)

5034802600.dxf

**Specifications** 

SPK-503480-001-001.pdf

PS-503480-001-001.pdf

# **Product Environment Compliance**

#### **Compliance**

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	© per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

# **Compliance Statements**

- EU RoHS
- REACH SVHC
- Low-Halogen

### **Industry Documents**

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### **Substances of Interest**

PFAS

## **EU RoHS Certificate of Compliance**

## Additional Product Compliance Information

#### **Part Details**

#### **General**

Status	Active
Category	FFC / FPC Connectors
Series	FBH1
Description	Easy-On FFC/FPC Connector, 0.50mm Pitch, FBH1 Series, Right- Angle, Dual Contact, 1.00mm Height, 26 Circuits, Gold over Nickel Plating
Comments	Black Actuator
Product Name	Easy-On
UPC	884982400528

### **Agency**

UL	E29179

#### **Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

## **Physical**

7.000.0.00	Actuator Type	Back Flip
------------	---------------	-----------

Circuits (Loaded)	26
Color - Resin	Natural (White)
Contact Position	Dual
Durability (mating cycles max)	10
Flammability	94V-0
Mated Height	1.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	85.621/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC/FPC

# **Solder Process Data**

Max-Duration	3
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	250

## Mates With / Use With

# Mates with Part(s)

Description	Part Number
0.50mm Pitch Premo-Flex FFC Jumpers	<u>15020</u>
0.50mm Pitch Premo-Flex FFC	<u>15120</u>

Li consissione di del	
iumpers	
Jampers	

This document was generated on Sep 23, 2025