

Snap-in markers - US-EMP (40X17)



0829437

<https://www.phoenixcontact.com/us/products/0829437>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, lettering field size: 40 x 17 mm, Number of individual labels: 16



Your advantages

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames

Commercial Data

Item number	0829437
Packing unit	1 pc
Minimum order quantity	10 pc
Note	Made to Order (non-returnable)
Sales Key	B12
Product Key	BG2419
Catalog Page	Page 317 (C-3-2019)
GTIN	4046356562218
Weight per Piece (including packing)	10.45 g
Weight per Piece (excluding packing)	8.05 g
Customs tariff number	39269097
Country of origin	DE

Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Technical Data

Product properties

Product type	Device marking
Marking	
Number of individual labels	16
Number of individual labels per row	2
Marking technology	
Device	5146464 THERMOMARK CARD 5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Printability	Thermal transfer

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10 ... 25 °C / 35 ... 65 % relative humidity. Storage in a cool and dry place is recommended.

Mounting

Mounting type	insert
---------------	--------

Material specifications

Color	white
RoHS compliant	Yes
Foil strength	300 µm
Material	PVC PVC
Flammability rating according to UL 94	V0
Components	Silicone-free
Silicone-free	yes

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
---------------	---------------------

Snap-in markers - US-EMP (40X17)



0829437

<https://www.phoenixcontact.com/us/products/0829437>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
--	--

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	following DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10 ... 25 °C / 35 ... 65 % relative humidity. Storage in a cool and dry place is recommended.
Recommended ambient temperature (storage/transport)	10 °C ... 25 °C
Recommended humidity (storage/transport)	35 % ... 65 %

Dimensions

Width	40 mm
Height	0.3 mm
Length	17 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Snap-in markers - US-EMP (40X17)



0829437

<https://www.phoenixcontact.com/us/products/0829437>

Classifications

ECLASS

ECLASS-9.0	27400629
ECLASS-11.0	27281106
ECLASS-10.0.1	27400629

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

Snap-in markers - US-EMP (40X17)



0829437

<https://www.phoenixcontact.com/us/products/0829437>

Accessories

Plastic cable markers

Plastic cable markers - KMK 4 - 1005305

<https://www.phoenixcontact.com/us/products/1005305>

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, lettering field size: 40 x 17 mm



Cable marker carrier

Cable marker carrier - KMK HP (40X17) - 0830723

<https://www.phoenixcontact.com/us/products/0830723>

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 9 mm, lettering field size: 40 x 17 mm



Snap-in markers - US-EMP (40X17)



0829437

<https://www.phoenixcontact.com/us/products/0829437>

Cable marker carrier

Cable marker carrier - KMK UV (40X17) - 1014109

<https://www.phoenixcontact.com/us/products/1014109>

Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 9 mm, lettering field size: 40 x 17 mm



Plastic cable markers

Plastic cable markers - KMK 3 - 1005211

<https://www.phoenixcontact.com/us/products/1005211>

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter range: 16 ... 35 mm, lettering field size: 40 x 17 mm



Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451

<https://www.phoenixcontact.com/us/products/5146451>

Magazine for the THERMOMARK CARD printer, for accommodating US cards



Magazine

Magazine - TMP-US-MAG1 - 0803341

<https://www.phoenixcontact.com/us/products/0803341>

Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards



Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371

<https://www.phoenixcontact.com/us/products/0801371>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BK 100 - 0803374

<https://www.phoenixcontact.com/us/products/0803374>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups UCT. ..., US..., and UM..., width: 110 mm, color: black

Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110/50-TC - 0801384

<https://www.phoenixcontact.com/us/products/0801384>



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BK 101 - 0803714

<https://www.phoenixcontact.com/us/products/0803714>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS..., width: 110 mm, color: black

Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 BU 100 - 0803378

<https://www.phoenixcontact.com/us/products/0803378>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: blue

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 GN 100 - 0803380

<https://www.phoenixcontact.com/us/products/0803380>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: green

Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 RD 100 - 0803377

<https://www.phoenixcontact.com/us/products/0803377>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: red

Ink ribbon cartridge

Ink ribbon cartridge - TMP-RIBBON 110 YE 100 - 0803379

<https://www.phoenixcontact.com/us/products/0803379>



Ink ribbon cartridge, for THERMOMARK PRIME for printing product groups US(2)-TM(F)...., US-TM(F)L...., US-WMTB...., US-EML...., US-EML(S)P...., US-EMLP-HA...., US-EM(S)P...., US-EML-RS...., width: 110 mm, color: yellow

Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Ink cartridge

Ink cartridge - BM ID-CARTR. BK - 1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

Ink cartridge

Ink cartridge - BM ID-CARTR. CY - 1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan

Snap-in markers - US-EMP (40X17)

0829437

<https://www.phoenixcontact.com/us/products/0829437>



Ink cartridge

Ink cartridge - BM ID-CARTR. YE - 1044348

<https://www.phoenixcontact.com/us/products/1044348>



Replacement UV fluid, 23 ml, color: yellow

Magazine

Magazine - BM ID-ADAPTER PLATE-US - 1044355

<https://www.phoenixcontact.com/us/products/1044355>



Adapter plate for accommodating US sheets

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com