

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301120095

Status:

Active

Overview:

Lighting Accessories

Description:

300W Guard Open-End without Reflector, Steel, Zinc Plated

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130112
NEMA Configuration	N/A
Outlet	None
Overview	Lighting Accessories
Product Name	Woodhead
Taxonomy	Portable Lighting Accessories
Type	Accessory
UPC	78678860885
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Open End, Steel
Height	N/A
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Net Weight	388.728/g
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	N/A
Lamp Type	A21
Lamp Wattage - Maximum	300W
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A
Material Info	
Engineering Number	1161

Image coming soon

Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130112 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION