**Part Number :** 191930330
**Product Description :** VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton
**Series Number :** 19193
**Status :** Active
**Product Category :** Ring and Spade Terminals
**Engineering Part Number :** H-381-14



## Documents and Resources

### Drawings

191930330_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-19902-011-001.pdf

PS-19902-013-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19193 |
| Description | VersaKrimp Ring Tongue Terminal for 1/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton |
| Keyword | Ring Terminal, Ring Terminals |
| Product Name | VersaKrimp |
| Style | Ring |
| Type | Ring Terminal, Metric Ring Terminal |
| UPC | 800755052008 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Electrical

| | |
|---|---|
| Voltage - Maximum | up to 35kV |

### Physical

| | |
|---|---|
| Barrel Type | Closed - Brazed |
| Insulation | None |
| Material - Metal | Copper |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Plating Mating | Tin |
| Net Weight | 21.319/g |
| Packaging Type | Carton |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Stud Size | 1/4" (M6) |
| Temperature Range - Operating | -50° to +149°C |
| Termination Interface Style | Crimp or Compression |
| Wire Size (AWG) | 1/0 |
| Wire Size $mm^2$ | 50.00 |

## Application Tooling

### Global

| Description | Part Number |
|---|---|
| Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices | 192860117 |
| Die Set (Large) for the HHLS Hydraulic Crimper | 192900011 |
| Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals | 192940008 |
| Square DIN Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG | 640038070 |
| Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices | 638162000 |



Downloaded from Arrow.com.