

Specification Sheet

Part Number: 109-00001



- Open-head design with easily detectable slot opening allows for swift and easy insertion
- Pre-lock feature allows for a temporary hold
- The large ribbed tail permits an ergonomic installation
- Two rails on the strap ensure guidance through the cable tie head

Q Tie, 4.1" Long, 18lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	109-00001
Type	Q18R
Color	Natural (NA)
Quantity Per	bag
Product Description	Q-Ties have a distinctive open-style head, a pre-lock function, and a large ribbed tail. The easily detectable slot opening offered with the tail and tie head provides ease of placement when working with gloves or for blind applications with limited view of the installation. The pre-lock feature allows for temporary holding of cable and wire bundles, permitting additional cables and wires to be placed without destroying the cable tie. Q-Ties can be tensioned by hand or with one of HellermannTyton’s mechanical cable tie application tools.
Short Description	Q Tie, 4.1" Long, 18lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name	Q18R-PA66-NA
------------------	--------------

Minimum Tensile Strength (Imperial)	18.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	80
-----------------------------------	----

Length L (Imperial)	4.1
---------------------	-----

Length L (Metric)	105
-------------------	-----

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.1
--------------------	-----

Width W (Metric)	2.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	0.9
--------------------------------	-----

Bundle Diameter Max (Metric)	24.0
------------------------------	------

Thickness T (Imperial)	0.039
------------------------	-------

Thickness T (Metric)	1.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 746B UL ANSI/UL 1565 UL ANSI/UL 62275
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)