



By Burndy
Catalog # [BIBS44](#)

Aluminum Multiple Tap Connector, Clear Insulated, 4 Port, 1 Sided Entry, 14-4 AWG, Al/Cu Rated



Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory

Application

For Indoor Use Only, Copper Or Stranded Aluminum

Specifications

EU RoHS Indicator	Yes
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - UL Listed Direct Burial	No
Buy American Compliant	Yes
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)

Conductor

Conductor - Copper Str Size Range	14 AWG - 4 AWG
Conductor Type	AL C Str-Size;CU C Str-Size
Conductor - AL Str Size Range	14 AWG - 4 AWG

Configuration

Physical Attribute - Number of Screws	4
---------------------------------------	---

Number Of Ports	4
-----------------	---

Current

Voltage - Maximum	600 V
Operating Voltage	600 V

Dimensions

Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm
Dimension - Height inch	1.25 in
Dimension - Height mm	31.8 mm
Dimension - Screw Size inch	1/4

General

Sub Brand	UNITAP
Physical Attribute - Screw Type	Allen
Insulation Type	Plastisol
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC 12 Digit	781810134122
UPC 14 Digit GTIN	00781810134122
Material	Aluminum
Hex Key	1/8
UPC	781810134122

Logistics

Carton Quantity	250
Minimum Pack Quantity	1

Operational

Temperature Rating	90° C
--------------------	-------

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)