

Part Number : 1301540058
Product Description : Watertite Extreme Standard Molded W Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA L5-15, 125V
Series Number : 130154
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 24W47-W

Documents and Resources

Drawings

1301540058_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130154
Description	Watertite Extreme Standard Molded W Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA L5-15, 125V
IP Rating	IP69K
NEMA Configuration	NEMA L5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Molded W Cordset
UPC	78678800636

Agency

CSA	LL52750
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No

Downloaded from Arrow.com.

Locking Blade	Yes
Net Weight	1.000/g
Poles	2-pole/3-wire
Receptacle Type	Triple

This document was generated on Sep 15, 2026

Downloaded from Arrow.com.