




1		2		3		4		5		6		7		8							
A																					
B																					
C																					
D																					
E																					
F																					
27		33614311000006		Fiber optic, multi mode 62.5/125 µm				100													
26		33614310900006						90													
25		33614310800006						80													
24		33614310700006						70													
23		33614310600006						60													
22		33614310500006						50													
21		33614310450006						45													
20		33614310400006						40													
19		33614310350006						35													
18		33614310300006						30													
17		33614310250006						25													
16		33614310200006						20													
15		33614310150006						15													
14		33614310140006						14													
13		33614310130006						13													
12		33614310120006						12													
11		33614310110006						11													
10		33614310100006						10													
9		33614310090006						9													
8		33614310080006						8													
7		33614310070006						7													
6		33614310060006						6													
5		33614310050006						5		All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing					
4		33614310040006						4		 All rights reserved Department HCS - RO		Created by COSTEA		Inspected by COSTEA		Standardisation MUNTEANV		Date 2018-07-19		State Final Release	
3		33614310030006						3				Title FO CA PP2-SCdx, 62,5µ, OM1									
2		33614310020006						2													
1		33614310010006						1		HARTING Customised Solutions D-32339 Espelkamp		Type TB		Number 3361431XXX0006		Rev. D		Page 2/2			
Cont. no.		Part no.		Type of cable				Dim. a[m]													
1		2		3		4		5		6		7		8							