



Part Number : [1110401404](#)
Product Description : QSFP+-to-QSFP+ Cable
Assembly, 30 AWG, 4.0m Length
Series Number : 111040
Status : Obsolete
Product Category : High-Speed I/O Cable
Assemblies



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains TBBA per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	High-Speed I/O Cable Assemblies
Series	111040
Description	QSFP+-to-QSFP+ Cable Assembly, 30 AWG, 4.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP+-to-QSFP+
Product Name	QSFP Plus,QSFP+
UPC	883906967536

Agency

UL	E72548
----	--------

Electrical

Impedance	100Ω
-----------	------

Physical

Cable Length	4.0m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	297.900/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Round
Wire Size (AWG)	30

This document was generated on Apr 26, 2025