

6

5

4

3




2

1


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/14	

APPROVED: _____


DATE: _____ TITLE: _____



SECTION A-A



SECTION B-B



SPECIFICATIONS:

Material: Phosphor Bronze

Thickness: 0.2mm

Wire range: AWG#22~#28

Plating:

G= Gold flash Plated

T= Tin Plated

Environmental:

Lead free, RoHS compliant.

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

2.00 PITCH CRIMP CONTACT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED							
INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .015	ØXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .010	ØXXX	± .010
APPROVALS				DATE			
DRAWN	AY		11/26/14	CHECKED	TW	11/26/14	APPROVED
SIZE				PART NO.			
X				2CTDD-X-R			
REF: S00188T				SCALE: NTS			
				SHEET 1 OF 1			

A

B

C

D

A

B

C

D

6

5

4

3

2

1