



Product: [8216](#) 

50 Ohm Wireless Transmission Coax, RG-174, 26 AWG Str BCCS, 90% TC Braid, PVC Jkt

Product Description

50 Ohm Wireless Transmission Coax, RG-174, 26 AWG (7x34) Bare Copper Covered Steel Conductor , PE Insulation, 90% Tinned Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

Construction Details

RG Type:	174
----------	-----

Conductor

Size	Stranding	Nom. Diameter	Material
26 AWG	7x34	0.019 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.060 in (1.5 mm)	White

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	90%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.110 in (2.79 mm)

Overall Cable Diameter (Nominal):	0.110 in (2.79 mm)
-----------------------------------	--------------------

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	1.9 dB/100ft
10 MHz	3.3 dB/100ft
50 MHz	5.8 dB/100ft
100 MHz	8.4 dB/100ft
200 MHz	12.5 dB/100ft
400 MHz	19.0 dB/100ft
700 MHz	27.0 dB/100ft
900 MHz	31.0 dB/100ft
1000 MHz	34.0 dB/100ft

Power Rating

Frequency	Max. Power Rating
1 MHz	976 W

10 MHz	354 W
50 MHz	197 W
100 MHz	161 W
200 MHz	136 W
400 MHz	120 W
700 MHz	112 W
900 MHz	109 W
1,000 MHz	108 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
97 Ohm/1000ft	10.7 Ohm/1000ft (35.1 Ohm/km)	30.8 pF/ft (101 pF/m)	50 Ohm	66%

Voltage

UL Voltage Rating	Voltage Rating
30 V (UL AWM 1354)	1100 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL AWM 1354)	-30°C to +75°C

Bend Radius

Installation Min.
1.1 in (28 mm)

Max. Pull Tension:	20 lbs (9.1 kg)
Bulk Cable Weight:	8 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor - Aerial, Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
AWM Compliance:	AWM 1354
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.539 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8216 010100	Black	Reel	100 ft	612825196266	
8216 010500	Black	Reel	500 ft	612825355496	
8216 0101000	Black	Reel	1,000 ft	612825196273	G N

Footnote:	G - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 100'. N - FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.
-----------	---

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.