

Representative Image

Catalog No. TY523M-NDT

Description: TIE 11lb 4" DRK BLUE NY DET-ANT

UPC No 786210995311

Home > Wire & Cable Management > Ty-Rap > Cable ties

Antimicrobial Detectable Cable Tie, Dark Blue Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 92mm (3.6 Inches), Width of 2.3mm (0.09 Inch), Thickness of 0.9mm (0.035 Inch), Maximum Bundle Diameter 16mm (0.63 Inch), Tensile Strength Rating of 50 Newtons (11 Pounds)

Descriptors

Category	Cable ties
Special Features	Detectable by metal detectors, X-ray equipment, or visual detection.

Specifications

Material	Nylon/Polyamide 6.6
Color	Blue
Lock Mechanism	Stainless Steel Barb
Tensile Strength	11 pounds , 50 newtons

Classifications

Brand Name	Ty-Rap

Dimensions

Width	0.09 in , 2.3 mm
Length	3.6 in , 92 mm
Thickness	0.035 in , 0.9 mm
Bundle Diameter	0.08 to 0.63 in , 2 to 16 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ2	N/A	N/A

by ABB

Downloaded from Arrow.com.