

P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	DRAFTING UPDATE	29OCT2020	SM	MZ
	A	PRODUCT UNDER TESTING	24NOV2020	SM	MZ
	A1	18AWG WIRE SIZE ADDED	27JAN2022	DM	SM
	A2	RELEASED	18MAR2022	SM	MZ

NOTES:

1 CONTACTS SUPPLIED SEPARATELY ON REELS, MUST PURCHASED ACCORDING TO WIRE SIZES. BELOW ARE THE CONTACT PART NUMBERS:

CONTACT P/N	WIRE SIZE
2359527-1	1.5mm ² TO 2.5mm ² 16AWG TO 14AWG
2359527-2	4.0mm ² 12AWG
2359527-3	18AWG

2. MATERIALS:






PLASTICS: PBT+PC ALLOY, UL-V0, UV-F1
CONTACTS: COPPER ALLOY, TIN PLATED
SCREWS : STAINLESS STEEL

3. OPERATING RATINGS :

VOLTAGE (max): 600Vac Max
CURRENT (max): 25A ON 4.0mm² & 20A ON 12AWG
TEMPERATURE : -40°C TO 85°C
IP RATING : IP67 & IP68

4. FOR ASSEMBLY INSTRUCTIONS, REFER APPLICATION SPECIFICATION 114-133123

5. PACKAGING: PPQ 200 pcs IN TRAY




2363547-2	2365125-2	KEY B	Ø 7 - Ø 10	IN-LINE SOCKET CONNECTOR	1-2379239-2
	2365125-1	KEY A			1-2379239-1
2363547-1	2365125-2	KEY B	Ø 10.5 - Ø 15		2379239-2
	2365125-1	KEY A			2379239-1
BACKSHELL P/N	HOUSING ASSY P/N	POLARIZING KEY	CABLE RANGE	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH. M 28AUG2020	 TE Connectivity		
		CHK M. ZUCCA 28AUG2020			
		APVD PETER OTT 24NOV2020			
		PRODUCT SPEC 108-133123			
		APPLICATION SPEC 114-133123	NAME NECTOR T, 3Pos, SOCKET CONNECTOR CRIMP TYPE		
		WEIGHT -	SIZE A3	CAGE CODE 00779	RESTRICTED TO -
		CUSTOMER DRAWING	DRAWING NO C-2379239	SCALE 2:1	REV A2


DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
	0 PLC	±0.2	
	1 PLC	±0.2	
	2 PLC	±0.1	
	3 PLC	±	
	4 PLC	±	
MATERIAL -		FINISH -	


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

CRIMP TERMINATION
REFER 114-133123 FOR DETAILED INSTRUCTION
NOT TO SCALE



EXPLODED COMPONENTS
NOT TO SCALE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH. M	28AUG2020	 TE Connectivity	
		CHK M. ZUCCA	28AUG2020		
DIMENSIONS: mm		APVD PETER.OTT	24NOV2020	NAME NECTOR T, 3Pos, SOCKET CONNECTOR CRIMP TYPE	
		PRODUCT SPEC 108-133123		SIZE A3	
		APPLICATION SPEC 114-133123		CAGE CODE 00779	
MATERIAL -		WEIGHT -		DRAWING NO C-2379239	
		CUSTOMER DRAWING		SCALE 2:1	SHEET 2 OF 2
				REV A2	RESTRICTED TO -