



PART FINDER

FIND NOW

Find faster what you're looking for!

Always a good connection

Search

Product Overview

Connectors

Customer specific solutions
D SUB
D SUB accessories
D SUB cover
DVI
Centronics
IDC
Modular
USB
USB 3.0 + USB 3.1
IEEE 1394
Power supply
DIN 41612
DIN 41617
Mini DIN
IC Socket

Pin and female header

LED connectors
Jumper
Connector sleeves
Solder terminals
Test terminals
Terminal Blocks
Memory Card connectors
FFC / FPC connectors
Micro-Miniature
Keystone Jack
Gender Changer
Modular Plug
Waterproof parts

Thermal management

Cable assembly

Capabilities

IT Network Products



download
technical drawing



download
Product Change Notification



3D view

Pin and female header

AWL254-DG-G16D
Pin-&female-header
pin-header dual row THT
16pins spacing 2,54mm straight
stamped contacts 11,54mm Au
polybag

Part number: AWL254-DG-G16D

product group: Pin-&female-header

style: pin-header

contact type: THT

pin count: 16

spacing in mm: 2,54

current rating: 3A

version: dual row

contact length: 11,54mm

contact direction: straight

plating: Au

contact machining: stamped contacts

packaging: polybag

process: THT

insulator: PBT UL94V-0

USB 3.1 Cable Assemblies with PD-funktion

Download the Newsletters



MORE NEWS



Company Film

Watch our company video!

[START WATCHING](#)

Contact

1840 W. Drake Drive, Suite 101
Tempe AZ, A
+1 (480) 8977 001
info@assmann-wsw-usa.com

[TO CONTACT](#)



[PART FINDER](#)

[IMPRINT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[PRIVACY POLICY](#)

[PRINT](#)

[RECOMMEND](#)