

Technical data sheet

Article number:
111-01564

T50R



Product Group	Cable Ties inside serrated
Material	Polyamide 12 (PA12)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	3.3 mm
Flammability	UL 94 HB
Length (L)	202.0 mm
Min.Tensile Strength	200 N
Operating Temperature	-40 °C to +120 °C
Package Content packed in	pack
Pack Cont.	1000 pcs.
Releasable Closure (Yes/No)	No
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64139
UV-resistant acc. to ASTM D6779 (Yes/No)	Yes
Variant	Inside Serrated
Width (W)	4.6 mm

