


P1


P2



PIN ASSIGNMENT	
P1	P2
1	1 RED
2	2 WHITE
3	3 GREEN
4+5	4 BLACK
SHELL	DRAIN + BRAID
	SHELL

- Material:**
- Cable: USB2.0 UL 27725 [28AWG(7/0.1 2 T.C+AL)X1P+28AWG(7/0.12TC)X2C]+AEB(48B TC)
 - Jacket: Black
 - OD: 3.5MM
 - Connector: Micro USB 5P A/M Solder Type
 - Shell: Nickel
 - Pin: G/F
 - Insulator Color: White
 - Outer Jacket: Black PVC-50P
- Electrical:**
- 100% Open short & mis wire test
 - Contact Resistance: 3Ω Max.
 - Insulation Resistance: 20MΩ Min.
 - Hi-Pot test: 300V DC



Scale	1:1	Name	Chappell	Item No.	AK67321-2-R
TOLERANCE		Drawn	10.19.11	Approved	
X.X	±0.40				
X.XX	±0.25				
X.XXX	±0.15				
Angle	±3°	Title USB2.0 Micro Connection Cable, 2 Meters USB A Micro Male <=> USB A Male Drawing No.			
					rev00
					Replace
					Sheet