

Products / Certified Peripherals / Monitor / Professional LCD Monitor / 96LED-24W-VS-B4 /

96LED-24W-VS-B4



- Full HD 1080p 1920 x 1080 resolution
- Ultra-fast 2 ms response time
- Low input lag for seamless experience
- Black stabilization for ultimate visibility
- DisplayPort, HDMI and VGA inputs for flexible connectivity; dual integrated speakers
- Energy-saving Eco-mode

Datasheet (PDF)

Get Quote

Product Specifications

Download S

Contact Advantech

Part Number	96LED-24W-VS-B4
Details	
Monitor	
Manufacturer	VIEWSONIC
Screen Size	24"
Resolution	1920 x 1080
Brightness	300 cd/m²
Contrast Ratio	1000:1
Viewing Angles (H/V)	170°/ 160°
Response Time (typical)	2 ms
Backlight	LED
Panel Type	TN
Wide Screen	Yes
Connectors	VGA, DisplayPort, HDMI
Video Input	Analog RGB; DVI
Built-in Speakers	Yes
Power Requirements	AC 100 - 240 V; 50 / 60 Hz
Power Consumption	24 W
Power Saving Mode	14 W
Ergonomics Tilt (Forward/Back)	5° / 23°
VESA Compatibility	100 x 100 mm
Color	BLACK
Dimensions (With Stand; W x H x D)	558.7 x 422.4 x 229.7 mm / 22.0 x 16.63 x 8.8 in.

Dimensions (Without Stand; W x H x D)	558.7 x 352.6 x 45.5 mm / 22 x 13.88 x 1.79 in.
Weight	3.63 kg / 8 lb.
Regulations	WEEE, RoHS Green BOM & DoC, CE EMC, CB, REACH SVHC List & DoC, EEL, ErP, Windows 8 & 10, UL, FCC-B w/ICES003, EPEAT Silver, ENERGY STAR, Mexico-CoC, Mexico Energy
Warranty	3 Years

Support

- [Datasheet \(PDF\)](#)
- [Technical Documents](#)



Need more info? Talk to our Online Rep!

[Live Chat](#)[Inquiry Form](#)

Related Materials

All

News (8)

Catalog (1)

ADVANTECH Online

-  [Buy Online](#)
-  [Live Chat](#)
-  [1-888-576-9668](#)

Contact Us

- [Price and Quotation](#)
- [RMA Service](#)
- [Technical Support](#)
- [Worldwide Offices](#)

Global eStore

- [eStore](#)
- [Retail Store](#)
- [Warranty Policy](#)

Popular Links

- [Advantech TALKs](#)
- [MyAdvantech Magazine](#)
- [Worldwide Events](#)
- [Solution Day](#)

About Advantech

- [Company Information](#)
- [Investor Relations](#)
- [Job Opportunities](#)
- [Citizenship Programs](#)

