



Color: ■ white

Technical data	
Marking method	Thermal transfer
Marking	plain
Delivery form	Roll
Delivery form configuration	800 pcs/reel; 2 lines
Properties	Inner wrap (inside marking area)
Printing device	Smart Printer (thermal transfer printer)
Physical data	
Height	15 mm
Width	117.5 mm
Depth	0.17 mm
Marking surface	97 x 15 mm
Mechanical data	
Mounting type	Mounting with cable ties
Smear resistance	in conjunction with 258-5005 Ink Ribbon
Material data	
Color	white
Material	Polyester
UV resistance	EN 60068-2-5:2010 Procedure B
Adhesive information	without adhesive
Halogen-free	Yes
Weight	600 g
Fire load	0 MJ



Environmental requirements		
Ambient temperature (storage)		+10 ... +21 °C
Ambient temperature (operation)		-30 ... +120 °C
Relative humidity		40 ... 50 %

Commercial data		
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4055143040891
Customs tariff number		39269097900

Product Classification		
UNSPSC		55121612
eCl@ss 10.0		27-40-04-01
eCl@ss 9.0		27-40-04-01
ETIM 9.0		EC001530
ETIM 8.0		EC001530
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 211-836		

Documentation				
Operating Instructions				
211-836 Information on printing material	1	28.08.2020	pdf 1467.39 KB	