




1 .000030 [0.00076] GOLD IN THE CONTACT AREA, .000100 [0.00254] TIN-LEAD ON THE TAILS OVER .000050 [0.00127] NICKEL ON THE ENTIRE CONTACT

21	-	1	1.980 [50.29]	1.700 [43.18]	1.425 [36.20]	19	2.090 [53.09]	2.380 [60.45]	40	443967-4
41	-	1	3.480 [88.39]	3.200 [81.28]	2.925 [74.30]	39	3.590 [91.19]	3.880 [98.55]	80	443967-2
16	-	1	1.605 [27.05]	1.325 [33.66]	1.050 [26.67]	14	1.715 [43.56]	2.005 [50.93]	30	443967-1
CAVITY IDENT			F	E	D	C	B	A	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES [mm]

MATERIAL
PER MIL-C-55302/23

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005 [0.13]
4 PLC ± -
ANGLES ± -

FINISH
- 1

DWN
C.C.THOMAS
CHK
D.MILLER
APVD
D.MILLER
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
-
CUSTOMER DRAWING

1/7/98
1-8-98
1-8-98
NAME
SIZE
CAGE CODE
DRAWING NO
A100779C=443967
SCALE
5:1

TE Connectivity

PIN HEADER ASSY,.075CL,
BOX WITH INTERNAL KEYING
-

RESTRICTED TO
-

SHEET
1
OF
1
REV
C