
Part Number : 1300610092
Product Description : BradPower A-Size (7/8”–M22) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 14 AWG, Gray PVC Cable, 3.0m (9.84') Length
Series Number : 130061
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 104000A46M030



Documents and Resources

Drawings

1300610092_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130061
Description	BradPower A-Size (7/8”–M22) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 14 AWG, Gray PVC Cable, 3.0m (9.84') Length
IP Rating	IP67
Product Name	BradPower A-Size
Type	Single Ended
UPC	78678880904

Agency

UL	E258922

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

Physical

Cable Diameter	14.99mm (.590")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Gray
Connector End A	BradPower A-Size (7/8”–M22)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC

Downloaded from Arrow.com.

Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	890.854/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	STOOW
Wire Size (AWG)	14

Downloaded from Arrow.com.