

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| DS | - |


REVISIONS


| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | A | RELEASED | 28/AUG/09 | SW | HG |









SECTION A-A




NOTES.

1. GENERAL TOLERANCE : ±0.3,±3°
2. ALL RADII ARE 0.3 EXCEPT AS INDICATED
3. MATING CONN'R : 967644
4. APPLIED TAB CONTACT, WIRE SEAL P/N : SEE TABLE1.
5. WARPAGE & FLASH : MAX 0.2






TABLE 1.


| | DESCRIPTION | P/N | WIRE SIZE (mm²) |
|---|---|---|---|
| MQS TAB | TAB CONTACT | 962886 | 0.2~0.5 |
| | | 965908 | 0.5~0.75 |
| | WIRE SEAL | 967067 | 0.2~0.75 |

| ASSY P/N | 2005342-5 |
|---|---|

| NO | COLOR | MATERIAL | DESCRIPTION | QTY |
|---|---|---|---|---|
| 3 | NATURAL | PBT-GF15 | PIN HSG | 1 |
| 2 | GREY | PA66-GF30 | SLIDE HSG | 1 |
| 1 | YELLOW | PBT-GF10 | CAP HSG | 1 |




DELIVERY CONDITION
RETAINER IN PRELOCKED POSITION



RETAINER IN END-LOCKED POSITION

SECTION B-B

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-

MATERIAL -
FINISH -

| | |
|---|---|
| DWN | SW NA |
| CHK | JW JUNG |
| APVD | HG CHO |
| PRODUCT SPEC | - |
| APPLICATION SPEC | - |
| WEIGHT | - |

Tyco Electronics
Tyco Electronics
Kyungsan Korea

NAME
CAP ASSY FOR MQS2P SEALED CONN'R

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C-2005342 | - |

CUSTOMER DRAWING

SCALE 1:1 SHEET 1 OF 1 REV A

Downloaded from Arrow.com.