



Part Number : [2048430001](#)
Product Description : Mirror Mezz
Hermaphroditic Connector, 2.50mm
Connector Height, BGA-Attach Mounting, 7
Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au)
Plating, without Pegs
Series Number : 204843
Status : Active
Product Category : Board-to-Board
Connectors



Documents & Resources


Drawings
[2048430001_sd.pdf](#)

3D Models and Design Files
[2048430001_stp.zip](#)
[2028281506EE-000.pdf](#)
[2028281506SP-000.zip](#)

Specifications
[2028280001-AS-000.pdf](#)
[2028289005PS-001.pdf](#)
[2028280001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 33; 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	204843
Description	Mirror Mezz Hermaphroditic Connector, 2.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs
Application	Board-to-Board, Mezzanine
Component Type	PCB Header
Product Name	Mirror Mezz
UPC	191128393027

Electrical

Current - Maximum per Contact	0.75A (1 Oz Cu Trace), 1.2A (2 Oz Cu Trace)
Voltage - Maximum	30V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	699
Circuits (maximum)	699
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No

Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	5.00mm
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	5.257/g
Number of Rows	11
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	1.50mm, 4.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	BGA Solder

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
-------------	-------------

Mirror Mezz Hermaphroditic Connector, 5.50mm Connector Height, BGA-Attach Mounting, 7 Pair, 11 Row, 699 Circuits, 0.76µm Gold (Au) Plating, without Pegs	<u>2034560003</u>
Mirror Mezz Hermaphroditic Connectors	<u>204843</u>
Mates With	This is a hermaphroditic, self-mating part.

This document was generated on Apr 19, 2025