
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

Need more information?

Detailed information about this product is not currently available on TE.com. Contact us for product documentation and for information about similar and replacement products.

CHAT NOW



✔ Active

TE CONNECTIVITY (TE)

STIFTKONT M5300Y60

1411582-2
TE Internal Number: 1411582-2
Alias ID: V23540M5300Y60

EU RoHS Compliant
EU ELV Compliant

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

CRIMP PIN 0.35/0.5
PDF **(TIFF AVAILABLE)**
German

Stiftkontakt 0.35/0.5
PDF **(TIFF AVAILABLE)**
German

Customer Drawing
PDF **(TIFF AVAILABLE)**
English

Downloaded from Arrow.com.

Product Specifications

Application Specification

Allgemeine Crimpspezifikation / GENERAL CRIMP SPEC.

PDF

German

Empfehlung Min. Leitungslaenge Bei Ultraschall-Schweissknoten / RECOMMENDATION MIN. WIRE LENGTH FOR ULTRASONIS WELD SPLICES

PDF

English

Product Specification

ELO Standard / Gedreht Kontaktsystem

PDF

German

ELO Standard / Rotated Contact System

PDF

German

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Detailed product features are not currently available online.

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.