All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon



Metal DC Geared Motor - 6V 162RPM 1.2Kg.cm

SKU:FIT0495-G Brand:Other Reward Points: 99

* Model: 15RPM | 20RPM | 73RPM | 97RPM | 162RPM | 191RPM | 357RPM

Quantity: - +

ADD TO CART

Frequently Bought Together

Metal DC Geared Motor - 6V 162RPM 1.2Kg.cm + ... Controller (L298N) + Rome... Bluetooth 4.0 + Gravity: 2x2A ... Twin + Copper Cou... (4mm) =

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

This is a metal DC geared motor, 45:1 metal reducer. It has a small size and large torque. The maximum torque could arrive 1.2 kg.cm. It is stable and durable!

Romeo BLE Application connection - DFRobot

Metal DC Geared Motor - DFRobot dimension

SPECIFICATION

- Rated Voltage: 6 V
- Operating Voltage Range 2~7.5V
- Gear reduction ratio: 45:1
- Gearbox length: 21 mm
- "D" shape shaft diameter: 4 mm
- No-load speed: 15 RPM @ 6V
- No-load current: 50 mA
- Locked-rotor torque: 1.2 Kg.cm
- Locked-rotor current: 0.6 A
- Operating Temperature: -20～60℃
- Weight: 68 g

SHIPPING LIST

Downloaded from Arrow.com.

- Metal DC Geared Motor - 6V 15RPM 10Kg.cm x1

REVIEW

FAQ

0 Comments DFRobot Disqus' Privacy Policy Login
Recommend Tweet Share Sort by Best
ırt the discussion...
Be the first to comment.
Subscribe Add Disqus to your site Do Not Sell My Data DISQUS

Sign up for exclusive offers!
Your email address →
Like us on

Downloaded from Arrow.com.