



All ECONOSEAL, CONNECTOR HOUSING (58)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 174369-2
070 SENSOR PLUG HSG 2P BLACK




TE Part # CAT-EC7491-T273
Econoseal Receptacles and Tabs


Customers Also Bought




TE Part #DT04-2P-EP04
REC, 2P, GRY, N, CAP




TE Part #219271-000
S02-15-R




TE Part #DTP04-4P-E004
REC, 4P, BLK, N




TE Part #42899-2
RING TONGUE 10-6 AWG TPBR




TE Part #60634-1
FF 250 REC 18-14AWG BR




TE Part #1-331401-1
SOLISTRAND RING 26-22 #6




TE Part #1-1394416-1
MT2,FL-KONTGEH 2X4P



TE Part #1456968-1
CONTACT,FEMALE, 0.64, 20 TO 22 AWG, AG



TE Part #1456968-2
CONTACT,FEMALE, 0.64, 18 AWG, AG



TE Part #2236048-1
KIT SEC.LOCK FOR 32 WAYS CONN.

Documents

Product Drawings
070 SENSOR PLUG ASSY 2P BLACK

Japanese

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_2822361-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2822361-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2822361-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Econoseal Connector Series](#)

English

Product Specifications

[Product Specification](#)

English

[Product Specification](#)

Japanese