

## 2-Port USB 3.0 SuperSpeed Desktop Extension Cable A (M/2xF), 6 ft. (1.83 m)

MODEL NUMBER: U324-006-DSK2



Converts your computer's USB 3.0 port to 2 USB 3.0 ports and extends them up to 6 ft away. Ideal for connecting thumb drives, digital cameras and other USB-A devices.

### Features

#### Expands an Existing USB 3.0 Port to 2 Ports and Extends Them an Extra 6 ft.

- Move a hard-to-reach USB port within easy access
- Ideal for connecting external hard drives, thumb drives, digital cameras and other USB-A devices
- Features one USB 3.0 data/power port and one power-only port

#### Enjoy SuperSpeed Transfer Rates in High-End Applications

- Supports data transfer rates up to 5 Gbps—10x the speed of USB 2.0
- Bi-directional interface allows data to flow both directions at the same time, increasing theoretical bandwidth by 10x
- Backward compatible with earlier USB generations

#### First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding blocks EMI/RFI interference
- Molded nickel-plated connectors ensure excellent connectivity
- Integral strain relief for cable and connectors' long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces
- Black padded non-sliding base

## Specifications

### OVERVIEW

### Highlights

- Supports data transfer rates up to 5 Gbps
- Bi-directional interface allows data to flow both directions
- Backward compatible with previous USB generations
- Features one USB 3.0 data/power port and one power-only port
- Double-shielded protection against EMI/RFI line noise
- Black padded non-sliding base

### System Requirements

- Computer, laptop or other device with USB 3.0 port (to achieve USB 3.0 speeds)

### Package Includes

- U324-006-DSK2 2-Port USB 3.0 SuperSpeed Desktop Extension Cable (M/2xF), 6 ft.

|                                       |                              |
|---------------------------------------|------------------------------|
| UPC Code                              | 037332199478                 |
| Technology                            | USB; USB 3.x                 |
| USB Cable Type                        | Passive                      |
| <b>INPUT</b>                          |                              |
| Maximum Input Amps                    | 2                            |
| <b>CHARGING</b>                       |                              |
| Total Charging Watts                  | 10                           |
| <b>PHYSICAL</b>                       |                              |
| Material of Construction              | PVC                          |
| Cable Jacket Color                    | Black                        |
| Cable Jacket Material                 | PVC                          |
| Cable Jacket Rating                   | VW-1                         |
| Cable Outer Diameter (OD)             | 5.5mm                        |
| Cable Length (ft.)                    | 6                            |
| Cable Length (m)                      | 1.83                         |
| Shipping Dimensions (hwd / in.)       | 5.31 x 3.94 x 0.50           |
| Shipping Dimensions (hwd / cm)        | 13.49 x 10.01 x 1.27         |
| Shipping Weight (lbs.)                | 0.24                         |
| Shipping Weight (kg)                  | 0.11                         |
| Unit Packaging Type                   | Polybag                      |
| <b>ENVIRONMENTAL</b>                  |                              |
| Operating Temperature Range           | 32 to 104 F (0 to 40 C)      |
| Storage Temperature Range             | 14 to 131 F (-10 to 55 C)    |
| Relative Humidity                     | 5% to 90% RH, Non-Condensing |
| Operating Humidity Range              | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range                | 0% to 90% RH, Non-Condensing |
| Power Provided to Connected Device(s) | 10W (5V/2A)                  |
| <b>CONNECTIONS</b>                    |                              |
| Side A - Connector 1                  | USB A (MALE)                 |
| Side B - Connector 1                  | (2) USB A (FEMALE)           |
| Connector Plating                     | Nickel                       |
| Contact Plating                       | Gold                         |

| FEATURES & SPECIFICATIONS           |                                           |
|-------------------------------------|-------------------------------------------|
| Data Transfer Rate                  | 5 Gbps                                    |
| Over Current Protection             | Yes                                       |
| USB Specification                   | USB 3.2 Gen 1 (up to 5 Gbps)              |
| STANDARDS & COMPLIANCE              |                                           |
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA); UKCA |
| WARRANTY & SUPPORT                  |                                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty                 |