C2G

Discontinued - 1ft (0.3m) Cat5e Snagless UTP Unshielded Ethernet Network Patch Cable (USA-Made) - Gray

Part No. CG-22829



100% manufactured and tested within the United States, this cable meets the stringent requirements for anyone who needs to procure products exclusively manufactured in the USA. For voice/data/video distribution, this cable will handle bandwidth-intensive applications. Meets all Cat5E TIA/EIA standards, and drastically reduces both impedance and structural return loss (SRL) .

Each of the individual pairs is bonded together to help maintain the twist-spacing throughout the line right up to the termination point.

Constructed from high quality cable and a shortened body plug, this design minimizes Near-End Crosstalk (NEXT) levels. Available in a variety of colors to easily color-code your network installation.

Features & Benefits

- Designed for network adapters, hubs, switches, routers, HDBaseT applications and more
- Supports 1 Gigabit networks up to 328ft for fast data transmission and maximum performance
- Meets all Cat5e TIA/EIA requirements for supporting a wide variety of applications
- Constructed with unshielded twisted pair (UTP) wires, designed to counter EMI, RFI, and crosstalk
- Snagless connector design for high density environments and protecting the RJ-45 connector's lock

Specifications

General Info

Product Line	C2G	Color	Gray
UPC Number	757120228295	Country Of Origin	China
Application Sector	Commercial, Industrial, Residential	Type	Cable

Dimensions

Cable Length	1 ft

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Application	Cat5e
Shielded/Unshielded Cable	Unshielded	Conductor	4-Pair Twisted
Shield Type	UTP	Cable Type	Ethernet Patch Cable
Jacket Rating	Standard / Non-Rated	Connector Type	Booted, Snagless
Indoor/Outdoor	Indoor	Connector 2	RJ-45 Male
Connector 1	RJ-45 Male		

Downloaded from Arrow.com.