

ENCLOSURE HARDWARE ▾

R13-24.0-RG

LED INDICATORS ▾

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDS

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING ▾

SOLUTIONS

RESOURCES ▾



ORCAdapt Flexible Pipe System, 1mm. Fiber Optic Core, 4.2mm. Dia. Low Profile Lens, 24.0in. Length, Square Bi-Color Red/Green LED



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES

VALUE ADDED

CHECK STOCK

- High Intensity Bi-Color LED, Red(4000mcd) Green (5000mcd)
- 4.2mm. Diameter Low Profile Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Front Panel Mount Lens



Enclosure Hardware

LED Indicators

LED Lighting

New Products

Locate a Distributor / Sales REP

Quality Assurance / RoHS

Product Info Center

Terms & Conditions

My Bivar



100% Employee Owned