



**Part Number :** [1300980066](#)  
**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male, Cable Diameter 7.93-9.53mm (.312-.375")  
**Series Number :** 130098  
**Status :** Active  
**Product Category :** Cable Grips  
**Engineering Number :** 5527

Documents & Resources

Product Environment Compliance

Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

|              |                                                                                                            |
|--------------|------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                     |
| Category     | Cable Grips                                                                                                |
| Series       | 130098                                                                                                     |
| Description  | MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male, Cable Diameter 7.93-9.53mm (.312-.375") |
| NEMA Rating  | NEMA 3R                                                                                                    |
| Product Name | MAX-LOC                                                                                                    |
| Type         | Strain Relief Grip                                                                                         |
| UPC          | 78678872158                                                                                                |

### Agency

|     |         |
|-----|---------|
| CSA | LR32159 |
| UL  | E76954  |

### Physical

|                            |                          |
|----------------------------|--------------------------|
| Approximate Break Strength | N/A                      |
| Bale Length                | N/A                      |
| Body Style                 | 90° Angle                |
| Cable Diameter             | 7.93-9.53mm (.312-.375") |
| Color - Grommet            | Gray                     |
| Eye Type                   | N/A                      |
| Gender                     | Male                     |
| Material - Body            | Nylon                    |
| Material - Grip            | N/A                      |
| Mesh Length                | N/A                      |
| Number of Holes            | 1                        |
| O-Ring                     | No                       |
| Thread Size                | 1/2" NPT                 |

## Mates With / Use With

### Use with Part(s)

| Description                                  | Part Number       |
|----------------------------------------------|-------------------|
| MAX-LOC Lock Nut 1/2" NPT                    | <u>1300990143</u> |
| MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black | <u>1300990149</u> |
| MAX-LOC O-Ring, 1/2" NPT                     | <u>1301800314</u> |

---

This document was generated on Sep 16, 2025